

CRANEFRIGOR™

Industrial Cooling since 1961

Made in Germany

TECHNICAL DESCRIPTION CRANEFRIGOR™ VB

Contact: e-mail: info@frigortec.de / phone: +49 7520 91482 - 0

Date: 30/04/2020 QVO 0447 Rev. 02



Figure

CRANEFRIGOR™ VB

The CRANEFRIGOR[™] VB liquefier was developed for reliable and long-term operation under extreme ambient conditions as in steel works, paper factories and foundries. Thanks to its robust structure, a reliable operation is ensured even with heavy shocks.

The CRANEFRIGOR[™] series of crane air conditioning units ensure a reliable and efficient production process.

The condensing unit CRANEFRIGOR[™] VB is only approved for evaporating temperatures > -10°C and is therefore not covered by Ecodesign Directive 2009/125/EC.



General description

Scope of delivery	Your benefits!
 Compressor (made by Bizer) Semi-hermetically sealed construction Suction-gas-cooled motor Self-regulating oil sump heater 	 Low maintenance No risk of overheating Ensures lubrication during the start Very good availability of spare parts worldwide
Liquefier Cathodic dip coating 	 High corrosion resistance Shorter maintenance intervals due to special adapted spacing between blades even with extreme dust load Shorter maintenance intervals due to smooth surface
 Liquefier fan Speed-controlled EC axial fan in industrial construction for high ambient temperatures 	PowerfulLong runtimesEnergy-efficient
 Casing Robust, welded construction Primed and powder-coated in RAL 3004 Other colours or stainless steel version optional 	 Robust, welded construction Primed and powder-coated in RAL 3004 Other colours or stainless steel version optional
 Terminal box Completely wired according to VDE Powder-coated RAL 7035 Optional stainless steel version 	 The CRANEFRIGOR™ is wired connection-ready on a terminal strip. Colour scheme with high corrosion protection
Quality assurance • Leakage test • Presetting of the safety devices	Operational reliabilityEasy commissioning on site



Options packages:

Material order no.	Scope of delivery	Your benefits!
807 539	Options packages "Corrosion protection" Corrosion protection package 1	Multiple-coated pipes
807 545	Corrosion protection package 2	 Housing / Plate parts made of high-quality stainless steel 1.4571 / AISI 316Ti Multiple-coated pipes
807 551	Option package "Custom" Customer-specific version	 Special requirements of a company can be realised, such as: Custom voltages / Network configurations Liquefier version (fully copper, blade spacing and thickness) Conductor identification Special coatings Protection class



Plant packages:

Material order no.	Scope of delivery	Your benefits!
807 571	 Plant packages "Electrical control" Constructed as switchboard or control cabinet Completely wired, according to VDE Operational and fault signal outputs Powder-coated RAL 7035 (control cabinet) 	Adjustable to individual specifications
807 572	Optional stainless steel version (Control cabinet)	Increased corrosion protection
807 565	Plant package "SMART Control" Superordinate controller FrigorTec Smart Control FSC	 Cyclic switching over for redundant systems Digital display of pressures and temperatures Optional regulation of the room pressure by filter/overpressure unit Optional display of the relative room humidity
807 573	 Plant packages "Internal unit (Evaporator)" Wall or ceiling version Operation of several internal units on one liquefier possible Epoxy-coated blades Housing primed and powder-coated 	 Adjustment options as required for the project Colour scheme with high corrosion protection
805 573	Optional housing in stainless steel version	Increased corrosion protection
807 562	Plant packages: "Overpressure / Fresh air" Filter/Overpressure unit FT15	 Filtered fresh air supply, adjustable air volume Creation of overpressure in the room to be cooled; less dust comes in
807 563	Self-cleaning filter/overpressure unit FS10	 Long filter service life due to fully automatic shaking function Filtered fresh air supply, adjustable air volume Creation of overpressure in the room to be cooled; less dust comes in
807 579	Plantpackage"Condensationevaporator"Condensation evaporator KV1	 No damage due to dripping condensation No additional power supply necessary Overload protection
807 575	 Plant package "Assembly material" Refrigerant lines made of copper Solenoid valves, expansion valves, filter drier, sight glasses Thermostats Insulation for suction line Refrigerant Plumb-line 	 Adjustments and planning as required for the project must be made in advance.

FRIGOR TEC

Technical specifications VB:

Performance data Cooling performance is included customised in the offer	
 Nominal cooling performance: At 27 °C room temperature, 52 % rel. room air humidity 35 °C ambient temperature Refrigerant R134a / R513A 	7 kW
 Cooling mode Depending on compressor size Depends on the option packages and version of heat exchanger 	
Temperature range R134a	-5 °C to +70 °C
Temperature range R513A	-5 °C to +70 °C
Temperature range R450A	-5 °C to +85 °C
- More extreme temperatures upon request	
Sizes and weight Weight Dimensions	approx. 150 kg type, see dimension sheet
Operating voltage Further operating voltages upon request	3 ph / 400 V / 50 Hz 3 ph / 460 V / 60 Hz
Protection category	IP54
Network type	TN-S
Refrigerant GWP (global warming potential)	R134a / R513A / R450A 1430 / 631 / 605
Filling quantity / CO2 equivalent	depends on the unit version
The performance description is a quality in the sense	of sections 434 and/or 633

The performance description is a quality in the sense of sections 434 and/or 633 BGB (German Civil Code). Subject to technical change.

FRIGOR TEC

According to (EN) 378-3 "Refrigeration units and Heat pumps – safety and environment regulations – Location and protection for persons" detectors needs to installed if concentration exceeds the practical limits (ATEL/ODL- EN 378-1, Appendix C) in a working and staying area.

The table is showing the minimum space dependent from the used Freon, air-conditioner and options.

Detectors are required if the conditioned space is smaller as mentioned in the table below.

Local restrictions and regulations need to be considered first.

Refrigerant	Minimum conditioned space before detector is required
R134a	20,8 m ³
R513A	16,3 m ³
R450A	13,9 m ³

ATEL: Exposure limit value for acute toxicity

ODL: Limit value for oxygen deficiency